



SATWipes® SAT-C3-7030 Wipes

Saturated nonwoven polyester wipes in center-pull dispenser

Description

The SATWipes C3 consists of a roll of saturated wipes that are dispensed through a convenient center-pull canister with a pop-up dispenser. The wipes consist of 100% nonwoven polyester fabric that is hydraulically entangled creating a soft, durable, and clean wipe. The saturation of 70% alcohol and 30% deionized water provides a safe, consistent, and mild cleaning solution. Eliminates solvent bottles, reduces solvent handling, and reduces solvent use by up to 35%. Refill rolls are available so the dispenser canister may be re-used.

Technical Data

Wipe material	100% polyester	
Wipe construction	Hydroentangled nonwoven	
Solution of saturation; (blend ratio and constituents)	70% isopropanol 30% ultra-pure deionized water	
Attribute; (units)	Value **	Test Method
Basis weight; (g/m ²)	69	
Non-volatile residue, NVR		IEST-RP-CC004.2, Sec. 6.1.2
In deionized water; (g/m ²)	0.055	
In isopropanol; (g/m ²)	0.008	
Specific ions		
Sodium; (ppm)	1.9	
Chloride; (ppm)	4.7	
Particles, readily releasable		IEST-RP-CC004.2, Sec. 5.1
P ≥ 0.5µm; (x10 ⁶ /m ²)	16.5	
Fibers > 100µm; (x10 ³ /m ²)	1.0	IEST-RP-CC004.2, Sec. 5.2
Saturation volume tolerance;		N/A
< 300 mL	+/- 12%	
300 -1666 mL	+/- 3%	
> 1666 mL	+/- 50 mL	

** ND = None detected; levels are below detection limit of test equipment

Part Number	Description	EA/RL	RL/PCH	PCH/CS	EA/CS
SAT-C3-7030	SATWipes polyester wipes, 70% IPA/ 30% DI water, 6" x 9" (15 x 23cm), canister w/ snap-close lid (SAT-CAN120)	100	1	12	1200
SAT-C3-7030/18	SATWipes polyester wipes, 70% IPA/ 30% DI water, 6" x 9" (15 x 23cm), no canister	100	1	18	1800
SWC30081	SATWipes polyester wipes, 70% IPA/ 30% DI water, 4.25" x 4" (11 x 10cm), with canister	185	1	12	2200

Key: EA = Each, RL = Roll, PCH = Pouch, OB1 = Outer Bag 1, CS = Case

Notes:

- 1) The information presented here is applicable to the part numbers shown above, as well as to any product containing the same materials and produced under the same conditions, regardless of product size or packaging configuration. Please contact a Contec sales representative for more details.
- 2) Data shown are typical values and should not be used as product specifications.
- 3) Valid product comparisons may only be obtained through side-by-side testing in the same test facility, under similar conditions.
- 4) Current and/or comparison data may be available. Please contact a Contec sales representative for details.

Revision date: 08/13/08



Copyright © 2008 Contec, Inc. All rights reserved.

North America
P.O. Box 530
Spartanburg, SC 29304 USA
Phone: +1-864-503-8333
www.contecinc.com

Europe
ZI du Prat – RP 3707
56037 VANNES Cedex
FRANCE
+33 297 437 690

China
No.17 Longyun Road
Suzhou 215024
CHINA
+ 86-512-6274 4050