



# VertiKlean<sup>®</sup> Mop Head

Single use foam mop head for VertiKlean Wall Washing System, **Regular**

### Description

The VertiKlean single use foam mop head is used with corresponding hardware for wet cleaning walls and ceilings and applying disinfectants in sterile and non-sterile environments. The laser-cut mop head consists of polyester fabric laminated to clean ester foam that provides excellent liquid sorbency as well as good abrasion resistance.

The VertiKlean Wall Washing System provides complete range of motion and is ideal for cleaning hard to reach areas such as corners and ceilings. Mop heads are available sterile per AAMI guidelines and compatible with a wide range of solutions and disinfectants. Recommended for single use due to possible cross contamination.

Compatible with frame part number 2651A.

### Technical Data

Mop head component materials (cleaning surface first)	Knitted polyester fabric/ 60ppi polyester foam	
Construction	Multi-layer; flame bonded/ inert hi-temp adhesive	
Actual Size	in cm	8L x 4W x 1H / 21L x 11W x 3H
<b>Attribute; (units)</b>	<b>Value **</b>	<b>Test Method</b>
Mop weight, dry; (g/mop)	34	CTM 004-03
Sorbency in water		CTM 004-03
Wet capacity; (mL/mop)	535	
Nonvolatile residue, NVR		CTM 006-01
In deionized water; (g/mop)	ND	
In isopropanol; (g/mop)	0.011	
Particles ≥ 0.5µm; (x10 <sup>6</sup> /mop)	0.70	CTM 005-01
Fibers > 100µm; (x10 <sup>3</sup> /mop)	0.06	CTM 005-01

\*\* ND = none detected; levels are below detection limit of test equipment

Part Number	Description	EA/OB1	OB1/OB2	OB2/CS	EA/CS
VK-MOP	Regular VertiKlean mop head	4	3	4	48
TVKMOP	Regular VertiKlean mop head, textured	4	3	4	48

Part Number	Description	EA/OB1	OB1/OB2	OB2/CS	EA/CS
VK-MOPIR	Regular VertiKlean mop head, sterile	1	4	12	48
TVKMOPIR	Regular VertiKlean mop head, textured, sterile	1	4	12	48

Key: EA = Each, OB1 = Outer Bag 1, OB2 = Outer Bag 2, CS = Case

Notes:

- 1) The information presented here is applicable to the part numbers shown above as well as to any product containing the same materials and produced under the same conditions, regardless of product size or packaging configuration. Please contact a Contec sales representative for more details.
- 2) Data shown are typical values and should not be used as product specifications.
- 3) Valid product comparisons may only be obtained through side-by-side testing in the same test facility, under similar conditions.
- 4) Current and/or comparison data may be available. Please contact a Contec sales representative for details.

Revision date: 11/09/15



Copyright © 2015 Contec, Inc. All rights reserved.

**North America**  
P.O. Box 530  
Spartanburg, SC 29304 USA  
Phone: +1-864-503-8333  
www.contecinc.com

**Europe**  
Zl du Prat – RP 3707  
56037 VANNES Cedex  
FRANCE  
+33 297 437 690

**China**  
No.17 Longyun Road  
Suzhou 215024  
CHINA  
+ 86-512-6274 4050