



VertiKlean[®] MAX[™] Microfiber mop head

Single use VertiKlean foam mop head with microfiber face, **Medium**

Description

The VertiKlean MAX single use microfiber mop head is used with VertiKlean hardware for wet cleaning and applying disinfectants to walls and ceilings in sterile and non-sterile environments. It's lightweight and easy to maneuver.

The microfiber fabric is laminated to a single layer of hydrophilic foam for unmatched absorbency. The ribbed microfiber face allows the mop to dislodge and remove contamination from surface. The foam head is backed by a semi-rigid thermoformed plate that easily snaps onto existing VertiKlean frames and provides uniform contact pressure on surfaces. Designed for one-time use, disposable mop heads are compatible with a wide range of solutions. VertiKlean MAX is also available sterile per AAMI guidelines.

Compatible with frame part number 2652A, 2652SS, 2652K.

Technical Data

Mop head component materials (cleaning surface first)		Knitted microfiber polyester fabric/100ppi hydrophilic urethane foam/knitted polyester fabric/APET thermoform backplate
Construction		Multi-layer; flame bonded/inert hi-temp adhesive
Actual Size	in cm	13.0L x 4W x 1H 32L x 11W x 2H

Attribute; (units)	Value **	Test Method
Mop weight, dry; (g/mop)	64.3	CTM 004-03
Sorbency in water		
Dry capacity; (mL/mop)	531	CTM 004-03
Non-volatile residue, NVR		CTM 005-01
In deionized water; (g/mop)	0.015	
In isopropanol; (g/mop)	0.034	
Particles ≥ 0.5µm; (x10 ⁶ /mop)	2.94	CTM 006-01
Fibers > 100µm; (x10 ³ /mop)	0.053	CTM 006-01

**ND = None detected; levels are below detection limit of test equipment

Part Number	Description	EA/OB1	OB1/OB2	OB2/CS	EA/CS
VKMX0225	Medium VertiKlean MAX Microfiber mop head	4	1	7	28

Part Number	Description	EA/OB1	OB1/OB2	OB2/OB3	OB3/CS	EA/CS
VKMX0275	Medium VertiKlean MAX Microfiber mop head, sterile	1	4	1	7	28

Key: EA = Each, OB1 = Outer Bag 1, OB2 = Outer Bag 2, OB3 = Outer Bag 3, CS = Case

Notes:

- 1) The information presented here is applicable to the part numbers shown above, as well as to any product containing the same materials and produced under the same conditions, regardless of product size or packaging configuration. Please contact a Contec sales representative for more details.
- 2) Data shown are typical values and should not be used as product specifications.
- 3) Valid product comparisons may only be obtained through side-by-side testing in the same test facility, under similar conditions.
- 4) Current and/or comparison data may be available. Please contact a Contec sales representative for details.

Revision date: 11/9/17
ETR3356



Copyright © 2017 Contec, Inc. All rights reserved.

North America
P.O. Box 530
Spartanburg, SC 29304 USA
Phone: +1-864-503-8333
www.contecinc.com

Europe
Zl du Prat – RP 3707
56037 VANNES Cedex
FRANCE
+33 297 437 698

China
No.17 Longyun Road
Suzhou 215024
CHINA
+ 86-512-6274 4050