



ANTICON[®]
BY CONTEC

When it has to be clean, it has to be Anticon[®] by Contec



**Anticon 100[®]
StandardWeight[™]**

High Sorbency Capacity for Spill Control

Lowest Fibers in a Cut Edge

Cleanroom Laundered

Anticon 100[®] StandardWeight[™]

100% Polyester double-knit interlock wipe with cut edges

DESCRIPTION

Anticon 100 StandardWeight wipes are made from 100% continuous filament polyester with a double-knit interlock construction. The clean cut edges exhibit low particle and fiber counts to minimize contamination. Using patented textile technology, Anticon 100 StandardWeight achieves superior capacity with a quick sorption rate.

FEATURES & BENEFITS

- Lowest fibers in a cut edge reduces risk of contamination
- Lighter basis weight provides superior value for general cleaning
- Manufactured from 100% continuous filament polyester and specially processed for superior cleanliness and sorbency
- Cleanroom laundered
- Tested in accordance with the IEST Recommend Practices for the Evaluation of Wiping Materials for Critical Environments
- Excellent for wiping and absorbing spills in a cleanroom environment
- Available in 9" x 9" and 12" x 12" sizes
- Offered in bulk and stacked packaging

ORDERING INFORMATION

Part #	Description	Packaging
495352-803	9" x 9" (23 x 23cm) 100 StandardWeight wipes	150 wipes/bag (2 inner bags of 75); 8 bags/case
495352-804	9" x 9" (23 x 23cm) 100 StandardWeight wipes, bulk	150 wipes/bag (2 inner bags of 75); 8 bags/case
495352-805	12" x 12" (31 x 31cm) 100 StandardWeight wipes	100 wipes/bag (2 inner bags of 50); 4 bags/case

Additional part numbers may be available. Ask your Contec representative for details.

KEY: Bulk= Advantage Pack



ANTICON®
BY CONTEC

Anticon 100®
StandardWeight™

TYPICAL TEST DATA			
Basis Weight		(gm/m ²)	120
Liquid Particles			
Biaxial Shake Test (IEST-RP-CC-004.2 Sec 5.2)	≥ 0.5 μm	(million particles/m ²)	10.0
	≥ 5.0 μm	(million particles/m ²)	0.06
Fiber Analysis			
ASTM F311-F312	> 100 μm	(fibers/m ²)	3097
NonVolatile Residue			
Short Term Extraction (IEST-RP-CC-004.2 Sec 6.1.2)	DI Water	(grams/m ²)	<0.007
	IPA	(grams/m ²)	<0.022
	Acetone	(grams/m ²)	<0.069
Sorbency			
Rate & Capacity (IEST-RP-CC-004.2 Sec 7.1 & 7.2)	Rate	(seconds)	<1
	Capacity	(ml/m ²)	400
Specific Ion Content			
Short Term Extraction (IEST-RP-CC-004.2 Sec 6.1.2)	Na	(μg/kg (ppb))	33
	Li	(μg/kg (ppb))	<1
	NH ₄	(μg/kg (ppb))	21
	K	(μg/kg (ppb))	80
	Mg	(μg/kg (ppb))	<1
	Ca	(μg/kg (ppb))	2
	Fl	(μg/kg (ppb))	19
	Cl	(μg/kg (ppb))	5

APPLICABILITY: This information is applicable to the following part numbers as well as to any product containing the same materials and produced under the same conditions, regardless of product size or packaging configuration. Please contact a Contec sales representative for more details.
495352-803, 495352-804, 495352-805

NOTES: This test data represents typical values and should not be used as product specifications. Valid product comparison may only be obtained through side-by-side testing in the same test facility, under similar conditions.